-DENIOS.

Selecting emergency showers

Find the right product for you!

Important factors in product selection:

- Installation sites (internal or external installation, availability of water and electricity connections, installation options)
- Vulnerable body areas
- Required rinsing time
- Water supply quantity
- Special requirements (use in hazardous areas, specific hygiene requirements)





	Eye rinse bottles	Eye shower with water connection	Chemical resistant body shower	Body shower with eyewash basin
Regulation complaint	EN-15154-4	EN-15154-2	EN-15154-1	EN 15154-1, EN 15154-2, EN 15154-5
Function	Release rinsing liquid by squeezing the bottle body	Activates via by pressure plate, valve lever or folding protection cover	Activates via pull bar	Activates by pull bar (body shower) or pressure plate or folding protection cover (eye shower)
Internal installation	✓	/	✓	✓
External installation	×	×	×	√ ∗
nstallation options	Mobile or wall mounted	Wall, table or floor mounted	Wall or ceiling mounted	Floor mounted
Water connection required	×	/	/	✓
Power source required	×	×	×	√ ∗
Flushes eyes	/	/	×	✓
Flushes body	×	×	/	✓
Rinsing time	2-5 minutes per eye	Unlimited	Unlimited	Unlimited
Water dispensing quantity	200 - 1.000 ml rinsing liquid	> 6 I/min	> 60I/min	Eyewash:> 6I/min Body shower:> 60 I/min
Made of hygienic stainless steel	×	√ **	/ **	/ **
Suitable for hazardous areas	×	×	×	/ ***
Special features	Can be transported to wherever it is needed. Can be wall mounted with integrated mirrors to make it easier to remove foreign objects.	Model with hose can be used both stationary (free hands) or flexible - to direct water source to injured parties.	Space-saving wall or ceiling mounting. Can be easily installed in any working environment.	Practical combination of eye and body shower. Also available in frost- proof, ex-protected versions.
	₩ Shop now >>	₩ Shop now >>	₩ Shop now >>	₩ Shop now >>

^{*} Frost-proof models with integrated heating ** Available in stainless steel *** ATEX rated model available